

# AGILA STAINLESS

7477PJC125P50

EAN 4031582349993  
Order number 00036345



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●●●

## CORE ATTRIBUTES

Product name	Agila stainless
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	160 mm
Overall width	60 mm
Overall weight	0.889 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing, stainless
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	41 mm
Swivel radius	131 mm
Swivel interference	262 mm
Dome diameter	60 mm
Stainless	✓

## FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm

# AGILA STAINLESS

7477PJC125P50

EAN 4031582349993  
Order number 00036345



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

