

LUMINA

A520PJI050L51-10 TFR

EAN 4031582389623



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------|
| Product name | Lumina |
| Housing type | Swivel castor |
| Load capacity at 3 km/h | 40 kg |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 56 mm |
| Overall width | 54 mm |
| Overall weight | 0.062 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 10 mm |
| Hardness of tread (A) | 88 Shore A |

HOUSING

| | |
|---------------------|---------------------------------------|
| Material fork | Polypropylene |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 62 mm |
| Swivel interference | 124 mm |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |