

AGILA

2471UAP125R05-28 M8/19

EAN 4031582301502



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Agila |
| Type | Swivel caster with directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 6.42 in |
| Overall width | 2.36 in |
| Overall weight | 2.74 lb |

HOUSING

| | |
|---------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 1.61 in |
| Swivel radius | 5.16 in |
| Swivel interference | 10.31 in |
| Dome diameter | 2.36 in |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

FITTING

| | |
|------------------------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 1.1 in |
| Bolt length | 1.77 in |
| Bolt thread position | 0.75 in |
| Bolt mounting holes quantity | 2 |

AGILA

2471UAP125R05-28 M8/19

EAN 4031582301502

Order number 00030255
Product Drawings



BETTER MOBILITY. BETTER LIFE.

