

LINEA LIGHT

5920UAI050P41-42X42/10

EAN 4031582454550



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Linea light |
| Housing type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 110.23 lb |
| Load capacity Static | 220.46 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 1.99 in |
| Overall width | 1.87 in |
| Overall weight | 0.13 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing with spacer tube |
| Threadguards | Without threadguard |
| Diameter | 1.97 in |
| Tread width | 0.51 in |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Offset | 0.59 in |
| Swivel radius | 1.81 in |
| Swivel interference | 3.62 in |
| Dome diameter | 0.91 in |

FITTING

| | |
|--------------------|--------------|
| Fitting type | Square plate |
| Bolt hole diameter | 0.39 in |

