

# LEVINA

5370JP125P50 7001

EAN 4031582347487



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Levina                    |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -10 °C                    |
| Temperature range (Maximum) | 40 °C                     |
| Overall Height              | 161 mm                    |
| Overall width               | 59 mm                     |
| Overall weight              | 0.57 kg                   |

## HOUSING

|                     |                       |
|---------------------|-----------------------|
| Housing Material    | Polyamide             |
| Fork shape          | Slim                  |
| Swivel Bearing      | Two ball races        |
| Housing Color       | Silver grey (RAL7001) |
| Offset              | 38 mm                 |
| Swivel radius       | 100.5 mm              |
| Swivel interference | 201 mm                |
| Dome diameter       | 59 mm                 |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread Material Mix    | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel Color           | Silver grey (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 32 mm                  |
| Body width            | 32 mm                  |
| Hardness of tread (A) | 87 Shore A             |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 46.5 mm           |
| Plate hole length (Maximum) | 51.5 mm           |
| Plate hole width (Minimum)  | 56 mm             |
| Plate hole width (Maximum)  | 61.5 mm           |
| Plate hole diameter         | 8.5 mm            |



Universal  
Design  
Award



Deutscher  
Designer  
Club

# LEVINA

5370PJP125P50 7001

EAN 4031582347487

Order number 00034258  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

