

AGILA TWIN

2970DIK050P30-11

EAN 4031582302646



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	132.28 lb
Electric conductive	no
Stainless	no
Load capacity Static	264.55 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	2.72 in
Overall width	2.09 in
Overall weight	0.69 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	0.98 in
Swivel radius	2.09 in
Swivel interference	4.17 in
Dome diameter	2.09 in

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.75 in
Body width	0.75 in
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

AGILA TWIN

2970DIK050P30-11

EAN 4031582302646

Order number 00030049

Product Drawings



BETTER MOBILITY. BETTER LIFE.

