

# STYLEA

5925UOI075S70-10X15 TFR

EAN 4031582385687



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	88 mm
Overall width	54 mm
Overall weight	0.157 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	87 mm
Swivel interference	174 mm
Thread diameter	10 mm

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	15 mm