

# STEM

S70-10x25 / 11 drilled stem

EAN 4031582411911



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	25 mm

## PERFORMANCE

Corrosion Resistance ●●●○○

## CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Overall Height	6 mm
Overall weight	0.05 kg