

AGILA LIGHT

1470PA0050P40

EAN 4031582335347
Order number 00900515



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila light |
| Housing type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 40 kg |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 70 mm |
| Overall width | 44 mm |
| Overall weight | 0.18 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 19 mm |
| Body width | 19 mm |
| Hardness of tread (A) | 91 Shore A |
| Hardness of tread (D) | 40 Shore D |

HOUSING

| | |
|---------------------|--------------------|
| Material | Steel sheet, light |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Colour | Blue passivated |
| Offset | 25 mm |
| Swivel radius | 50 mm |
| Swivel interference | 100 mm |
| Dome diameter | 41 mm |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 60 mm |
| Plate width | 60 mm |
| Plate hole length (Minimum) | 38 mm |
| Plate hole length (Maximum) | 48 mm |
| Plate hole width (Minimum) | 38 mm |
| Plate hole width (Maximum) | 48 mm |
| Plate hole diameter | 6.3 mm |

AGILA LIGHT

1470PAO050P40

EAN 4031582335347
Order number 00900515



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

