

# LINEA SAFETY

592DUAP075L51-10 7001/7015

EAN 4031582378269  
Order number 00771095



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Linea safety
Type	Automatic locking system
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	75.5 mm
Overall width	55 mm
Overall weight	0.186 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Tread color	Slate grey (RAL7015)
Wheel color	Slate grey (RAL7015)
Threadguards	With threadguard
Diameter	75 mm
Tread width	15 mm
Axle hole diameter	0 mm
Hub length	0 mm
Body width	15 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	Silver grey (RAL7001)
Offset	23 mm
Swivel radius	65 mm
Swivel interference	130 mm
Dome diameter	30 mm
Hint	Force to release 23 N and spring stroke length 8 mm.

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award

# LINEA SAFETY

592DUAP075L51-10 7001/7015

EAN 4031582378269  
Order number 00771095



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

