

PRODUCT INFORMATION

NOVATECH

ETP085x90-Ø17 HL90

EAN 4031582369465



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	85 mm
Tread width	90 mm
Axle Hole Diameter	17 mm
Hub Length	90 mm
Hardness of tread (A)	92 Shore A
Bearing type	6303

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	800 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

NOVATECH

ETP085x90-Ø17 HL90

EAN 4031582369465



BETTER MOBILITY. BETTER LIFE.

Product Drawings

