

AGILA LIGHT

1475POO050P30-11

EAN 4031582335822



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila light
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	70 mm
Overall weight	0.1 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	50 mm
Tread width	18 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	Two ball races
Offset	25 mm
Swivel radius	64 mm
Swivel interference	128 mm

FITTING

Fitting type	Bolt hole
--------------	-----------

PRODUCT INFORMATION

AGILA LIGHT

1475POO050P30-11

EAN 4031582335822



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

