

# KAPPA LOAD

9652ITP250P63 FLAT KICK PEDAL

EAN 4031582445305



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa load
Housing type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1000 kg
Load capacity Static	2000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	305 mm

## WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	250 mm
Tread width	55 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	61 mm
Swivel radius	187 mm
Swivel interference	374 mm

## FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# KAPPA LOAD

9652ITP250P63 FLAT KICK PEDAL

EAN 4031582445305



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

