

DELTA TWIN

9940ETP080P63

EAN 4031582428711



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Delta twin |
| Housing type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 500 kg |
| Load capacity Static | 1000 kg |
| Temperature range (Minimum) | -30 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 125.5 mm |
| Overall weight | 3.189 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Steel, iron |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Threadguards | With threadguard |
| Diameter | 80 mm |
| Tread width | 40 mm |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Iron forged, heavy |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Offset | 40 mm |
| Swivel interference | 176 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 137 mm |
| Plate width | 105 mm |
| Plate hole length (Maximum) | 105 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 11 mm |

DELTA TWIN

9940ETP080P63

EAN 4031582428711



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

