

AGILA

2470UOK050P30-11

EAN 4031582301250



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	69 mm
Overall weight	0.189 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	24 mm
Swivel radius	49 mm
Swivel interference	98 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

AGILA

2470UOK050P30-11

EAN 4031582301250



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

