

# ZETA

4681ITP160P63 SH80XL

EAN 4031582400465



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Zeta
Type	Swivel castor with directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1212.54 lb
Load capacity at 3.7 mph	970.03 lb
Load capacity Static	2425.08 lb
Temperature range (Minimum)	31.4 °F
Overall height	7.87 in
Overall weight	7.46 lb

## WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	2.17 in
Swivel interference	14.17 in

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

# ZETA

4681ITP160P63 SH80XL

EAN 4031582400465



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

