

AGILA

2470DYK100P30-11

EAN 4031582341607
Order number 00006519



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| CO2 emission (scope 3) | 1.75 kg CO2e |
| Housing type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 176.37 lb |
| Electric conductive | ✓ |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 185 °F |
| Overall height | 5.31 in |
| Overall width | 2.36 in |
| Overall weight | 1.85 lb |

WHEEL

| | |
|-----------------------|--|
| Body material | Sheet Steel |
| Tread material | Solid rubber, black, electric-conductive |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Color | Blue passivated |
| Offset | 1.5 in |
| Swivel radius | 3.46 in |
| Swivel interference | 6.93 in |
| Dome diameter | 2.36 in |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.43 in |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA

2470DYK100P30-11

EAN 4031582341607
Order number 00006519



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

