

FORMA

694GUF150P33 L1-L30 DARK GREY

EAN 4031582476415



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Forma
Housing type	Swivel castor with central locking (directional lock, free, wheel lock)
Load capacity at 3 km/h	135 kg
Temperature range (Minimum)	-18 °C
Temperature range (Maximum)	120 °C
Overall height	202 mm

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	18 mm
Hardness of tread (A)	60 Shore A

HOUSING

Material fork	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	57 mm
Swivel radius	137 mm

FITTING

Fitting type	Rectangular plate
Plate length	92 mm
Plate width	64 mm
Plate hole length (Maximum)	73 mm
Plate hole width (Maximum)	43 mm
Plate hole diameter	9 mm

FORMA

694GUF150P33 L1-L30 DARK GREY

EAN 4031582476415



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

