

LUMINA

AA20POI050S70-10x15/8 9011/9011

EAN 4031582415094



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	56 mm
Overall width	55 mm
Overall weight	0.13 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	20 mm
Swivel radius	52 mm
Swivel interference	104 mm
Dome diameter	0 mm
Thread diameter	10 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread Color	Graphite black (RAL9011)
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	7 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	7 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm

LUMINA

AA20POI050S70-10x15/8 9011/9011

EAN 4031582415094



BETTER MOBILITY. BETTER LIFE.

Product Drawings

