

AGILA

2470DIK050B10-11x31

EAN 4031582300598



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Swivel caster |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 88.18 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 176.37 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 185 °F |
| Overall height | 2.83 in |
| Overall width | 1.69 in |
| Overall weight | 0.52 lb |

HOUSING

| | |
|---------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 0.94 in |
| Swivel radius | 1.93 in |
| Swivel interference | 3.86 in |
| Dome diameter | 1.61 in |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 1.97 in |
| Tread width | 0.75 in |
| Body width | 0.75 in |
| Hardness of tread (A) | 80 Shore A |

FITTING

| | |
|---------------|----------------------------------|
| Fitting type | Stem with grip ring, with collar |
| Stem diameter | 0.43 in |
| Stem length | 1.22 in |

AGILA

2470DIK050B10-11x31

EAN 4031582300598

Order number 00004472
Product Drawings



BETTER MOBILITY. BETTER LIFE.

