

LINEA LIGHT

5925UAI065L51-10

EAN 4031582403886



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Linea light |
| Housing type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 132.28 lb |
| Load capacity Static | 264.55 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 2.68 in |
| Overall width | 1.81 in |
| Overall weight | 0.25 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing with spacer tube |
| Threadguards | Without threadguard |
| Diameter | 2.56 in |
| Tread width | 0.55 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 2.64 in |
| Swivel interference | 5.28 in |
| Dome diameter | 0.91 in |

FITTING

| | |
|--------------------|----------------------------|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in |



Deutscher Designer Club



Interzum Award



IF Design Award

LINEA LIGHT


5925UAI065L51-10

EAN 4031582403886



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award