

LUMINA

A520POI050P41-42x42

EAN 4031582344998



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	66 mm
Overall width	54 mm
Overall weight	0.05 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel Bearing	Stem, swiveling
Swivel radius	48 mm
Swivel interference	96 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	7 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Square plate
Plate length	42 mm
Plate width	42 mm
Plate hole length (Maximum)	32 mm
Plate hole width (Maximum)	32 mm
Plate hole diameter	5 mm