

LUMINA

AA25PJI050P41-38X38/10

EAN 4031582409994



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.52 in
Overall width	2.17 in
Overall weight	0.24 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.39 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	2.48 in
Swivel interference	4.96 in

FITTING

Fitting type	Square plate
Plate length	1.5 in
Plate width	1.5 in
Plate hole length (Maximum)	1.06 in
Plate hole width (Maximum)	1.06 in
Plate hole diameter	0.2 in