

# OMIKRON TWIN

9950FTP250P65

EAN 4031582316803  
Order number 00801479



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Omikron twin
Type	Swivel castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	3000 kg
Load capacity at 6 km/h	2400 kg
Load capacity Static	4500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	325 mm
Overall width	189 mm
Overall weight	27.897 kg

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Colour	Transparent coating
Offset	70 mm
Swivel radius	201.5 mm
Swivel interference	403 mm
Lubrication nipple	✓
Dome diameter	160 mm

## FITTING

Fitting type	Medium rectangular heavy-duty plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	160 mm
Plate hole diameter	15 mm

# OMIKRON TWIN

9950FTP250P65

EAN 4031582316803  
Order number 00801479



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

