

AGILA

2478XSP150P50

EAN 4031582344776



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Housing type | Fixed castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric conductive | ✓ |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 185 mm |
| Overall weight | 0.83 kg |

WHEEL

| | |
|-----------------------|---|
| Body material | Polyamide, electric conductive |
| Tread material | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 32 mm |
| Hardness of tread (D) | 40 Shore D |

HOUSING

| | |
|---------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 77 mm |
| Plate width | 67 mm |
| Plate hole length (Minimum) | 56 mm |
| Plate hole length (Maximum) | 61.5 mm |
| Plate hole width (Minimum) | 46.5 mm |
| Plate hole width (Maximum) | 51.5 mm |
| Plate hole diameter | 8.5 mm |

AGILA

2478XSP150P50

EAN 4031582344776



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

