

LUMINA

AA20POI050S70- 8X15 (30)

EAN 4031582458930



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Lumina |
| Housing type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 40 kg |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 58 mm |
| Overall width | 55 mm |
| Overall weight | 0.105 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 8 mm |
| Hardness of tread (D) | 65 Shore D |

HOUSING

| | |
|---------------------|----------------------------|
| Material fork | Polypropylene |
| Fork shape | Twin wheel housing, closed |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 49 mm |
| Swivel interference | 98 mm |
| Thread diameter | 8 mm |

FITTING

| | |
|--------------|--------------------------------------|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem length | 15 mm |