

LINEA

5908UAP150P63

EAN 4031582457018



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Linea
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Electric conductive	✓
Load capacity Static	300 kg
Overall height	175.5 mm
Overall width	89 mm
Overall weight	1.15 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	22 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Offset	0 mm

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm



Deutscher Designer Club



Interzum Award



IF Design Award

LINEA



5908UAP150P63

EAN 4031582457018



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award