

PRODUCT INFORMATION

# FOOTMASTER

FOOT MASTER GDN- 60-S-NYN

EAN 4031582413151



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel caster
Load capacity at 1.8 mph	551.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	551.16 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	3.25 in
Overall width	2.76 in
Overall weight	1.54 lb

## HOUSING

Housing Color	White
Offset	1.5 in
Swivel radius	2.48 in
Swivel interference	4.96 in
Dome diameter	2.76 in

## WHEEL

Bearing	Roller bearing, damped
Wheel color	Black
Diameter	1.97 in
Tread width	0.98 in
Body width	0.98 in

## FITTING

Bolt hole diameter	0.47 in
--------------------	---------

# FOOTMASTER

FOOT MASTER GDN- 60-S-NYN

EAN 4031582413151

Order number 00062077

Product Drawings



BETTER MOBILITY. BETTER LIFE.

