

KAPPA

9688ITP150P63 CL67

EAN 4031582316469
Order number 00829812



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	650 kg
Load capacity at 6 km/h	520 kg
Load capacity Static	1300 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	200 mm
Overall width	98 mm
Overall weight	3.389 kg

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	150 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Iron forged, heavy
Fork shape	Broad, reinforced
Colour	Blue passivated
Dome diameter	96 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA

9688ITP150P63 CL67

EAN 4031582316469
Order number 00829812



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

