

AGILA LIGHT

1477PAO100P30-11

EAN 4031582331516
Order number 00900106



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila light
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	125 mm
Overall width	44 mm
Overall weight	0.328 kg

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Plain bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

HOUSING

Material	Steel sheet, light
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	28 mm
Swivel radius	87 mm
Swivel interference	174 mm
Dome diameter	41 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm