

KAPPA FLEX

9750ITP160P63 SH80

EAN 4031582414288



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa flex
Type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	992.08 lb
Load capacity at 3.7 mph	661.39 lb
Load capacity Static	1984.16 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	8.66 in
Overall weight	10.96 lb

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	With spring
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	2.72 in
Swivel radius	5.87 in
Swivel interference	11.73 in

FITTING

Fitting type	Rectangular plate
Plate length	5.59 in
Plate width	4.37 in
Plate hole length (Minimum)	3.9 in
Plate hole length (Maximum)	4.41 in
Plate hole width (Minimum)	2.91 in
Plate hole width (Maximum)	3.27 in
Plate hole diameter	0.5 in