

# LINEA LIGHT

5925PJI075L51-10 RAL7001

EAN 4031582377521  
Order number 00770535



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Linea light                    |
| Housing type                | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 3 km/h     | 60 kg                          |
| Load capacity Static        | 120 kg                         |
| Temperature range (Minimum) | -20 °C                         |
| Temperature range (Maximum) | 60 °C                          |
| Overall height              | 75.5 mm                        |
| Overall width               | 55 mm                          |
| Overall weight              | 0.167 kg                       |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Threadguards          | Without threadguard            |
| Diameter              | 75 mm                          |
| Tread width           | 15 mm                          |
| Hardness of tread (A) | 92 Shore A                     |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Offset              | 23 mm              |
| Swivel radius       | 81 mm              |
| Swivel interference | 162 mm             |
| Dome diameter       | 30 mm              |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 10 mm                      |



# LINEA LIGHT



5925PJI075L51-10 RAL7001

EAN 4031582377521  
Order number 00770535



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award