

AGILA

2475PJP050P30-11 TNL

EAN 4031582327410



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Agila |
| Housing type | Swivel castor with wheel brake |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 40 kg |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 69 mm |
| Overall weight | 0.159 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 50 mm |
| Tread width | 19 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|----------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 24 mm |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 11 mm |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA

2475PJP050P30-11 TNL

EAN 4031582327410



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

