

KAPPA LOAD

9652FTP200P64 KICK PEDAL

EAN 4031582455786



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa load
Type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1680 kg
Load capacity at 6 km/h	1400 kg
Load capacity Static	3360 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	255 mm

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	200 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	65 mm
Swivel radius	183 mm
Swivel interference	366 mm
Lubrication nipple	✓

FITTING

Fitting type	Large rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	140 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	15 mm

KAPPA LOAD

9652FTP200P64 KICK PEDAL

EAN 4031582455786



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

