

# AGILA STAINLESS

7470W00075P30-11

EAN 4031582472523



BETTER MOBILITY. BETTER LIFE.

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila stainless
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity at 3.7 mph	165.35 lb
Electric conductive	✓
Stainless	✓
Load capacity Static	330.69 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	392 °F

## WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in

## HOUSING

Material	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	0.94 in
Swivel interference	4.84 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in
Hint	Castors can be mounted with standard screws of any length.