

# KAPPA LOAD

9658TOP200P63 TFR

EAN 4031582386356



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa load
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1200 kg
Load capacity at 6 km/h	1000 kg
Load capacity Static	2400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	245 mm
Overall weight	4.074 kg

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Lubrication nipple	✓

## FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# KAPPA LOAD

9658TOP200P63 TFR

EAN 4031582386356



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

