

# KAPPA LOAD

9658TOP200P63 TFR

EAN 4031582386356



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Kappa load                   |
| Housing type                | Fixed castor                 |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 1200 kg                      |
| Load capacity at 6 km/h     | 1000 kg                      |
| Load capacity Static        | 2400 kg                      |
| Temperature range (Minimum) | -40 °C                       |
| Temperature range (Maximum) | 80 °C                        |
| Overall height              | 245 mm                       |
| Overall weight              | 4.074 kg                     |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide, heavy          |
| Tread material        | Identical with wheel body |
| Bearing               | Precision ball bearing    |
| Axle                  | Screwed with nut          |
| Threadguards          | Without threadguard       |
| Diameter              | 200 mm                    |
| Tread width           | 50 mm                     |
| Hardness of tread (D) | 75 Shore D                |

## HOUSING

|               |                    |
|---------------|--------------------|
| Material fork | Iron forged, heavy |
| Fork shape    | Broad, reinforced  |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 135 mm            |
| Plate width                 | 110 mm            |
| Plate hole length (Maximum) | 105 mm            |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 80 mm             |
| Plate hole diameter         | 11 mm             |

# KAPPA LOAD

9658TOP200P63 TFR

EAN 4031582386356



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

