

COMPACTA

1298UOI014P80-26

EAN 4031582300024



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	15 kg
Electric Conductive	No
Stainless	No
Load capacity Static	30 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	13.5 mm
Overall width	19 mm
Overall weight	0.01 kg

HOUSING

Housing Material	Steel sheet, light
Fork shape	Straight
Housing Color	Blue passivated
Dome diameter	19 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	14 mm
Tread width	14 mm
Body width	14 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Round plate
Plate hole length (Maximum)	20 mm
Plate hole width (Maximum)	20 mm
Plate hole diameter	2.5 mm

COMPACTA

1298UOI014P80-26

EAN 4031582300024

Order number 00021119

Product Drawings



BETTER MOBILITY. BETTER LIFE.

