

PRODUCT INFORMATION

# NOVATECH

FTP 160X50-Ø20 HL60

EAN 4031582329551  
Order number 00801166



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2425.08 lb
Load capacity at 3.7 mph	1984.16 lb
Load capacity Static	3968.32 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	5.78 lb

# NOVATECH

FTP 160X50-Ø20 HL60

EAN 4031582329551  
Order number 00801166



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

