

# GALEA

5077YGH125R05-22X40 7001/7042 SCREWED

EAN 4031582354287



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●●○

## CORE ATTRIBUTES

Product name	Galea
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	✓
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.38 in
Overall width	2.56 in
Overall weight	1.45 lb

## WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing
Tread color	Traffic gray A (RAL7042)
Wheel color	Traffic gray A (RAL7042)
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.18 in
Axle hole diameter	0 in
Hub length	0 in
Body width	1.18 in
Hardness of tread (A)	90 Shore A

## HOUSING

Material	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races
Color	Silver gray (RAL7001)
Offset	1.57 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Dome diameter	2.32 in

## FITTING

Fitting type	Solid stem, round
Bolt diameter	0.87 in
Bolt length	1.57 in

# GALEA

5077YGH125R05-22X40 7001/7042 SCREWED

EAN 4031582354287



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

