

LUMINA

6A20YGI050L51-8

EAN 4031582311334
Order number 00078776



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Electric conductive	✓
Load capacity Static	176.37 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.13 in
Overall width	2.17 in
Overall weight	0.31 lb

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.39 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Zinc-die-casting / Aluminum
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	2.01 in
Swivel interference	4.02 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.31 in

PRODUCT INFORMATION

LUMINA

6A20YGI050L51-8

EAN 4031582311334
Order number 00078776



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

