

# STEM

S70-8x25 / 10

EAN 4031582424669



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

|               |                                      |
|---------------|--------------------------------------|
| Fitting type  | Threaded stem with hexagon neck, top |
| Stem diameter | 8 mm                                 |
| Stem length   | 25 mm                                |

## PERFORMANCE

Corrosion Resistance ●●●○○

## CORE ATTRIBUTES

|                         |           |
|-------------------------|-----------|
| Product Name            | Stem      |
| Type                    | Accessory |
| Load capacity at 3 km/h | 50 kg     |
| Electric Conductive     | No        |
| Stainless               | No        |
| Load capacity Static    | 100 kg    |
| Overall Height          | 6 mm      |
| Overall weight          | 0.03 kg   |