

KAPPA LOAD

9658TOP250P63 TFR

EAN 4031582386363



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa load
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2910.1 lb
Load capacity at 3.7 mph	2425.08 lb
Load capacity Static	5820.2 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	12.01 in
Overall weight	10.45 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
	✓

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

KAPPA LOAD

9658TOP250P63 TFR

EAN 4031582386363



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

