

AGILA STAINLESS

7470PJO100P30-13

EAN 4031582350166
Order number 00036322



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Agila stainless
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	135 mm
Overall width	60 mm
Overall weight	0.503 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm
Dome diameter	60 mm
Stainless	✓

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm
Hint	Castors can be mounted with standard screws of any length.

AGILA STAINLESS

7470PJO100P30-13

EAN 4031582350166
Order number 00036322



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

