

LUMINA

A520PJ1050L51-8 9011/7042

EAN 4031582317329
Order number 00073407



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.2 in
Overall width	2.13 in
Overall weight	0.14 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Traffic gray A (RAL7042)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.39 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.39 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Color	Graphite black (RAL9011)
Offset	0.79 in
Swivel radius	2.05 in
Swivel interference	4.09 in
Dome diameter	0 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.31 in

PRODUCT INFORMATION

LUMINA

A520PJI050L51-8 9011/7042

EAN 4031582317329
Order number 00073407



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

