

COMPACTA

2198U00023P40 60x45



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	33.07 lb
Electric conductive	no
Stainless	no
Load capacity Static	66.14 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	1.02 in
Overall weight	0.2 lb
Wheel width	1.5 in

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	0.55 in
Tread width	0.55 in
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	2.36 in
Plate width	1.77 in
Plate hole length (Minimum)	0.94 in
Plate hole length (Maximum)	1.61 in
Plate hole width (Maximum)	0.79 in
Plate hole diameter	0.16 in