

KAPPA

9688TOO250P63

EAN 4031582316629
Order number 00805788



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2910.1 lb
Load capacity at 3.7 mph	2645.54 lb
Load capacity Static	5820.2 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	12.01 in
Overall weight	9.71 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
	✓

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

KAPPA

9688TOO250P63

EAN 4031582316629
Order number 00805788



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

