

COMPACTA

1530PJO050P41

EAN 4031582428407



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	23 kg
Load capacity Static	46 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	60 mm
Overall weight	0.084 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	23 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	22 mm
Swivel radius	47 mm
Swivel interference	94 mm

FITTING

Fitting type	Square plate
Plate length	37 mm
Plate width	37 mm
Plate hole length (Maximum)	30 mm
Plate hole width (Maximum)	30 mm