

AGILA

2477YGO125R47-27-30

EAN 4031582341690



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Agila |
| Housing type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric conductive | ✓ |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 163 mm |

WHEEL

| | |
|-----------------------|---|
| Body material | Polypropylene, electric conductive |
| Tread material | Thermoplastic rubber, electric-conductive |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 41 mm |
| Swivel radius | 131 mm |
| Swivel interference | 262 mm |

FITTING

| | |
|----------------------------|--|
| Fitting type | Synthetic expander, square |
| Expander fitting (Minimum) | 27 mm |
| Expander fitting (Maximum) | 30 mm |
| Hint | Please indicate required tube innerdiameter when ordering. |

AGILA

2477YGO125R47-27-30

EAN 4031582341690



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

