

# KAPPA

9688TOO250P63

EAN 4031582316629  
Order number 00805788



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1320 kg
Load capacity at 6 km/h	1200 kg
Load capacity Static	2640 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	305 mm
Overall weight	4.404 kg

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced

## FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# KAPPA

9688TOO250P63

EAN 4031582316629  
Order number 00805788



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

